

# Small volume containers

## AGIL Range (series 0.5 to 6)



AGIL Range		AGIL 0.5	AGIL 1	AGIL 1/L	AGIL 2	AGIL 3	AGIL 6
<b>FEATURES</b>							
Usable capacity	l	0.5	1	1	2	3	6
Interior diameter	mm	65	85	100	100	185	185
External diameter	mm	87	107	122	122	200	200
Empty weight	kg	0.56	0.95	0.80	1.35	1.78	2.40
Total height	mm	203	231	177	312	190	300
Static holding time at 20°C with cork lid <sup>(1)</sup>	h	12	26	15	43	23	49
Daily theoretical evaporation rate at 20°C without cork lid <sup>(1)</sup>	l/d	1	0.9	1.6	1.1	3.1	2.9
<b>PRODUCT REFERENCES</b>							
<b>AGIL range (supplied without cork lid)</b>		<b>AGIL05-2</b>	<b>AGIL1-2</b>	<b>AGIL1L-2</b>	<b>AGIL2-2</b>	<b>AGIL3-2</b>	<b>AGIL6-2</b>
<b>REFERENCES FOR PRIMARY ACCESSORIES</b>							
<b>A</b> : Cork lid (optional)		<b>ACC-AGIL-1</b>	<b>ACC-AGIL-2</b>	<b>ACC-AGIL-3</b>	<b>ACC-AGIL-3</b>	<b>ACC-AGIL-4</b>	<b>ACC-AGIL-4</b>
<b>B</b> : Protective glasses		<b>ACC-SECU-2</b>	<b>ACC-SECU-2</b>	<b>ACC-SECU-2</b>	<b>ACC-SECU-2</b>	<b>ACC-SECU-2</b>	<b>ACC-SECU-2</b>
<b>C</b> : Protective gloves (Size 8)		<b>ACC-SECU-15</b>	<b>ACC-SECU-15</b>	<b>ACC-SECU-15</b>	<b>ACC-SECU-15</b>	<b>ACC-SECU-15</b>	<b>ACC-SECU-15</b>
Protective gloves (Size 9)		<b>ACC-SECU-16</b>	<b>ACC-SECU-16</b>	<b>ACC-SECU-16</b>	<b>ACC-SECU-16</b>	<b>ACC-SECU-16</b>	<b>ACC-SECU-16</b>
Protective gloves (Size 10)		<b>ACC-SECU-17</b>	<b>ACC-SECU-17</b>	<b>ACC-SECU-17</b>	<b>ACC-SECU-17</b>	<b>ACC-SECU-17</b>	<b>ACC-SECU-17</b>
Protective gloves (Size 11)		<b>ACC-SECU-18</b>	<b>ACC-SECU-18</b>	<b>ACC-SECU-18</b>	<b>ACC-SECU-18</b>	<b>ACC-SECU-18</b>	<b>ACC-SECU-18</b>

### Primary accessories



(1) Assessment of static holding times are done in agreement with conditions described within ISO 21014 norm extrapolated to assessed volumes according to theoretical models. Daily evaporation and static holding time at 20°C, 1 013 mb, immobile container. These values are nominal and can vary according to history of the container and manufacturing ranges.